

Data Sheet

300pcs 3:1 Adhesive lined Color Heat shrink tube-assortment

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. 300 pieces of shrinking ration 3:1 standard shrinking tube for a range of application diameter from 1.6 to 12.7 mm. Hot-melt adhesive lined tubing in the multi-color. The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.

Shrinking ratio	3 : 1
Material	PE
Shrinking temperature	70°C - 125°C
Operation temperature	-40°C - 125°C
Flammability	VW-1
Tensile strength	≥ 10.4Mpa
Elongation at break	≥ 300%
Rated voltage	600V
Diselectric strength	≥ 15 kV/mm at 30sec.
Volume resistivity	≥ 10 ¹⁴ Ω



Contents

Color	Heat shrink tube		Length	pcs
	Inner diameter ø	after shrink ø		
Red	1.6 mm	0.5 mm	60 mm	100
Blue	2.4 mm	0.8 mm	60 mm	70
Yellow	3.2 mm	1.0 mm	60 mm	50
Green	4.8 mm	1.5 mm	60 mm	30
Transparent	6.4 mm	2.2 mm	60 mm	20
Brown	7.9 mm	2.7 mm	60 mm	10
White	9.5 mm	3.2 mm	60 mm	10
Black	12.7 mm	4.2 mm	60 mm	10