

DECT business telephone

Aastra 630d

Aastra 630d is the new ruggedized DECT business phone. It is dust and jet water protected and may be used outside or in rough industrial environments.

The device satisfies the industrial standard IP 65. It is very easy to clean and complies with high hygiene requirements, making it ideally suited for the healthcare sector, too. With its integrated sensor alarm the phone is ideal for security professions or the prison and detention centres. An additional emergency call key makes the 630d the ideal companion not just for security-related professions, but also for hospitals and care facilities.

Service facilities like firmware download over air help reducing support costs.¹

The handset is equipped with a Bluetooth® interface for cordless headsets and comes with an option for a higher capacity battery. Furthermore the GAP standard is supported.



Aastra 630d

Highlights of the Aastra 630d

- ✦ TFT-colour display (2", 176 x 220 dots; 65,536 colours)
- ✦ Telephone book with 200 contacts¹, with 7 possible entries each: office, private, mobile and fax number, email address¹; ringing tone and quick dialling assignment¹
- ✦ Ambient noise filter for loud environments
- ✦ 44 polyphone (midi type) and 8 normal ring tones with automatic volume control can be assigned
- ✦ Up to 5 user profiles for e.g. headset or meeting usage can be configured
- ✦ Hands free operation
- ✦ Headset connector (2.5 mm jack) and Bluetooth® headset support
- ✦ 1 programmable Hotkey for numbers or functions
- ✦ 2 programmable navigation keys¹
- ✦ 3 programmable side keys
- ✦ 1 emergency key on top
- ✦ Intelligent battery management
- ✦ Mini USB PC interface
- ✦ 3 colour multi-purpose LED, which can be set for visualisation of functions

¹ if supported by PABX

Administration Features

- ✦ Automatic firmware update over air¹
- ✦ Integrated diagnostic functions

Local Features

- ✦ Illuminated keypad
- ✦ Different ring tones for: internal / external calls, messages, alarm call, emergency call¹
- ✦ Ring tone volume adjustable
- ✦ Ring tone off (shortcut: * key)
- ✦ Key lock (shortcut: # key)
- ✦ 3 soft keys for menu control (two of which are programmable¹)
- ✦ Signal tones for key click, confirmation, battery empty, out of range
- ✦ Different earpiece-, speaker-, headset volume
- ✦ 3 character fonts for text display in different sizes
- ✦ Display with 7 text lines, 1 headline and 1 soft key line
- ✦ Handset name can be edited
- ✦ Display brilliancy adjustable
- ✦ Colour scheme can be selected
- ✦ Illumination time for display and keypad can be adjusted separately

- ✦ Background light of the display can remain on for selectable intervals with dim function
- ✦ Alarm- and appointment settings for 3 different times each¹
- ✦ Automatic quick dialling by pressing numeric key¹
- ✦ Automatic / manual key lock
- ✦ Telephone lock with 4-digit PIN
- ✦ Automatic answer when removed from the charger
- ✦ Silent charging
- ✦ Trembler for vibra-call
- ✦ Caller list with 50 entries¹
- ✦ Redial list with 30 entries¹
- ✦ Display languages: Czech, Danish, Dutch, German, English, Finnish, French, Italian, Norwegian, Polish, Portuguese, Russian, Slovene, Spanish, Swedish¹
- ✦ Keys for volume control
- ✦ Time and date (manually or by PABX¹)
- ✦ Man down, no movement and escape alarm

Technical Data

- ✦ Standards: DECT, GAP
- ✦ Ingress protection: IP 65

- ✦ Supports DECT-encryption
- ✦ Standard Battery (SB): Lithium-Ion battery pack
- ✦ Power Battery (PB): Lithium-Ion battery pack
- ✦ Stand-by-time
SB: Up to 100 h EMEA / 95 h US
PB: Up to 200 h EMEA / 190 h US
- ✦ Talk time
SB: Up to 12 h EMEA / 15 h US
PB: Up to 24 h EMEA / 30 h US
- ✦ Battery compartment screw locked
- ✦ TPE armed surface (sides and top)
- ✦ Moisture protected foil key pad
- ✦ Free fall: 2 m on concrete without damage
- ✦ Dimensions (W x H x D):
53 x 135 x 22.5 mm
- ✦ Weight with standard batteries: 137 g
- ✦ International AC-adapter for EMEA, North America and Australia
- ✦ Compatible with commercial USB chargers

Tools

- ✦ PC tool for the telephone book¹; available in the download area of the Aastra website

Part numbers

- ✦ Handset with belt clip, standard battery, cradle, international AC-adapter and quick user guide
68849
- ✦ Cradle with international AC-adapter
68980
- ✦ Handset Aastra 630d with standard battery
68981
- ✦ Power battery
68773
- ✦ Battery cover for power battery
68771
- ✦ Belt clip "Rotary"
68668
- ✦ Lanyard attachment
68769
- ✦ Leather pouch
68761
- ✦ Mini USB cable
68759
- ✦ Charger Rack including 8 Rack Charger
68774



Aastra 630d in leather pouch



Charger Rack including 8 rack charger

¹ if supported by PABX

Aastra Technologies Limited

155 Snow Blvd.
Concord, Ontario Canada
L4K 4N9
www.aastra.com

Reference 04/2011



Copyright © 2011 Aastra Technologies Limited. Aastra and the Aastra logo are trademarks or registered trademarks of Aastra Technologies Limited in the United States, Canada, European Union and other countries. Picture similar to product. The right for technical modifications is reserved.

AASTRA