

Binoculars with camera TG-125

Binoculars with integrated digital camera



1.3 MP

1.3 MP Kamera /
1.3 MP Camera

10x

10-fache Vergrößerung /
10 times magnification

101m-1000m

Sichtfeld von 101m auf 1000m /
Field of view 101m at 1000m

32 GB

MicroSD Karte bis zu 32GB /
MicroSD card up to 32GB

2x

2 austauschbare AA Batterien (nicht mitgeliefert) /
2 replaceable AA batteries (not included)

1280x960

Fotoauflösung von 1280x960 pixel /
Photo resolution of 1280x960 pixels



- Magnification of 10 times
- Field of view of 101m at 1000m
- Telescope focus range of 3m to infinity
- Camera focus range of 50m to infinity
- HD Photo resolution
- VGA Video resolution
- MicroSD card up to 32GB (not included)

Technical specifications:

- Magnification: 10 times
- Lens diameter: 25mm
- Field of View: 101m at 1000m
- Sensor Type: CMOS
- Effective pixels: 1.3 Million
- Photo file size: 1280x960
- Video resolution / frame: 640x480 / 30fps
- Photo / Video / Audio format: JPEG / MPEG / 16Bit
- Connection: Mini-USB
- Memory expansion: Up to 32GB (not included)
- Weight / Dimensions: 230g / 17.2x13.5x6.5cm
- Power supply: 2x AA Batteries (LR6, Lithium, NiMH) (not included)

Package Contents:

- TrendGeek TG-125
- Mini-USB cable
- Cleaning cloth
- User manual



Article-No. 4790

