

INSTRUCTION MANUAL

ITEM: OUTDOOR WALL LAMP
Modell No.: VT - 7641
SKU: 7506



! WARNING

- Ensure that the power is switched off before installation.
 - Install only by certified electrician.
 - Keep this manual handy for future references
-

TECHNICAL PARAMETERS:

Input Voltage:	AC220-240V,50Hz
Holder	GU10 35W(MAX)
Protection Rating	IP44
Unit size	105*76*118mm

INSTALLATION INSTRUCTIONS:

- Drill two holes on the wall and insert two plastic expansion bolts in it.
- Fix the plastic plate on the plastic expansion piece with self-tapping screws.
- Connect the supply leads with terminal.
- Open the lamp and install the bulb in the lamp.
- Fix the lamp body on the plate and tighten the screws
- Switch on and test.

