

## INSTALLATION INSTRUCTION

ITEM: OUTDOOR WALL LAMP

Model: VT-7652

SKU: 7509



### **!Warning**

- Ensure that the power is switched off before installation.
- Install only by certified electrician.
- Keep this manual handy for future references

## **INTRODUCTION**

Thank you for selecting and buying V-TAC LED Outdoor Wall Lamp. V-TAC will serve you the best. Please read these instructions carefully before starting the installation and keep this manual handy for future reference. If you have any other query, please contact our dealer or local vendor from whom you have purchased the product. They are trained and ready to serve you at the best.

### TECHNICAL PARAMETERS

|                    |                   |
|--------------------|-------------------|
| Input Voltage:     | AC: 220-240V,50Hz |
| Holder:            | GU10 2 X 20W(MAX) |
| Protection Rating: | IP44              |
| Unit Size:         | 92*68*150mm       |

### INSTALLATION INSTRUCTIONS

- Fix the metal plate on the plastic expansion piece with self-tapping screws.
- Connect the supply leads with terminal.
- Open the lamp and install the bulb in the lamp
- Fix the lamp body on the plate and tighten the screws.
- Switch on and test.

