





TECHNICAL INFORMATION

Input Power:	DC:6V
LED Chip Type:	SMD
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	120°
Color:	4000K
Dimension:	1m
Sensor Type:	PIR
Detection Range:	2-5m
Battery Type:	4xAAAA
Watts per meter:	2.4
Lumens per meter:	200
No. Of Led:	30
Roll Qty:	1m



FEATURES

- IP65 Sensor Striplight(DC:6V) built with 1 Meter and power of 2.4W
- Functions on 4xAAA Battery(Battery Not Included)
- Built with PIR motion sensor
- Detection range of Min 2M up to 5 M
- Eay to Install No wiring required
- Suitable for Cabinets, Bedlight, Shelf Lighting and many more.



STRIPLIGHT 2835 SENSOR | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 2574 - 2938 View more details

PACKAGING

Gross Weight (Kgs): 0.106
Unit CBM: 0.001008
Dimension: 1m

MASTER BOX PACKAGING

Box Qty: 50
Qty Per Pallet: 2000
Length (Box) mm: 30
Width (Box) mm: 160
Height (Box) mm: 210

LISTING DETAILS

Commodity Code: 9405403990 EanCode: 3800157639347