


Distributed by Conrad Electronic SE • Klaus-Conrad-Str. 1 • D-92240 Hirschau

Datasheet

Item no. 1909641, 1909642, 1909643

V1_09062017_01_en



Flat Ribbon Cable

American Wire Gauge:	26AWG
Cable Shape:	Ribbon
Capacitance:	50 pF/m
Characteristic Impedance:	100 Ohm
Conductor Strand Type:	Stranded
Core Strands:	7x0.16 mm
Number of Strands:	7
Sheath Colour:	Multicoloured
Operating Temperature Range:	-20 to +105° C
Pitch:	1.27mm
Voltage Rating:	300V dc
Standards Met:	UL1007

BN	Number of ways	Reel length
1909641	10 pins	10 M
1909642	10 pins	30 M
1909643	20 pins	10 M

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.