

Armytek Predator Pro v3 / XHP35 HI Warm Tactical flashlight

SKU: F01703BW | EAN-13: 6957713001432

Detailed description:

- incredible light output 1570 LED lumens and excellent beam range up to 435 meters;
- clear central 5° spot and minimal 40° spill;
- constant brightness;
- due to the standard body diameter the flashlight is compatible with various weapon mounts;
- trouble-free operation of the flashlight at a 50 meters depth for 5 hours;
- original remote switch for comfortable hunting;
- 200 days runtime on one battery;
- IP68 water- and dustproof standard.

Additional features:

LED: Cree XHP35 High Intensity

Power source: 1x18650 Li-Ion / 2x18350 Li-Ion* / 2xRCR123 Li-Ion* / 2xCR123A

Number of modes: 9

Length: 154mm

Body diameter: 25.4mm

Head diameter: 41mm

Weight (without batteries): 135g

Package Set: flashlight, 2 rubber rings, rubber grip, holster, lanyard, 2 O-rings, spare rubber button, user manual

Manufacturer warranty: 10 years no-hassle warranty

* It is allowed to use only protected Li-Ion batteries.

Contact us in any way convenient for you!

Armytek Optoelectronics Inc. Wholesale Department

13-85 West Wilmot St
Richmond Hill, Ontario
L4B 1K7, Canada

+1 (289) 379-9933
world@armytek.com
www.armytek.com



Set description:

