

Armytek Dobermann Pro / XHP35 HI White Tactical flashlight

SKU: F02102BC | EAN-13: 6957713001524

Detailed description:

- incredible 1700 LED lumens light output and excellent light range up to 395 meters;
- clear focused light for long distance illumination;
- trouble-free operation of the flashlight at a depth of 50 meters;
- can be applied with the original remote button switch for attaching to the weapon and easy hunting;
- record runtime - 1 hour in max mode and up to 200 days in Firefly mode;
- perfectly matched brightness modes;
- IP68 water- and dustproof standard.

Additional features:

LED: Cree XHP35 High Intensity

Power source: 1x18650 Li-Ion / 2x18350 Li-Ion* / 2xRCR123 Li-Ion* / 2xCR123A

Number of modes: 9

Length: 140mm

Body diameter: 25.4mm

Head diameter: 34mm

Weight (without batteries): 115g

Package Set: flashlight, 2 rubber rings, rubber grip, holster, lanyard, 2 O-rings, spare rubber button, user manual

Manufacturer warranty: 10 years no-hassle warranty

* It is allowed to use only protected Li-Ion batteries.

Contact us in any way convenient for you!

Armytek Optoelectronics Inc. Wholesale Department

13-85 West Wilmot St
Richmond Hill, Ontario
L4B 1K7, Canada

+1 (289) 379-9933
world@armytek.com
www.armytek.com



Set description:

