

## Armytek Barracuda Pro v2 / XHP35 HI White Search and rescue flashlight

SKU: F03302SC | EAN-13: 6957713001760

### Detailed description:

- extreme light output 1850 LED lm and unprecedented beam distance 800 meters;
- simple operation and continuous runtimes - 1 hour at maximal mode and almost 22 hours at middle mode;
- convenient to mount under the barrel;
- practical plastic case;
- IP68 water- and dustproof standard;
- powerful electronics with constant brightness technology;
- energy saving technology of the step-by-step brightness control;
- the highest IP68 dust- and waterproof standard - more than 5 hours at 50 meters depth;
- guaranteed durability - stands up the recoil of any gun gauge and falling from 30 meters height.

### Additional features:

LED: Cree XHP35 High Intensity

Power source: 2x18650 Li-Ion\* or 1x18650 Li-Ion

Number of modes: 9

Length: 245mm

Body diameter: 25.4mm

Head diameter: 64mm

Weight (without batteries): 259g

Package Set: plastic case, flashlight, body 1x18650, rubber grip, holster, lanyard, 2 spare O-rings, spare rubber button, user manual

Manufacturer warranty: 10 years no-hassle warranty

\* It is allowed to use only protected Li-Ion batteries.

Contact us in any way convenient for you!

Armytek Optoelectronics Inc. Wholesale Department

13-85 West Wilmot St  
Richmond Hill, Ontario  
L4B 1K7, Canada

+1 (289) 379-9933  
world@armytek.com  
www.armytek.com



### Set description:

