

Accessories
AIMESA VRM 6,20**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

- for automatic stripping of individual wires
- stripping of flexible wires according to DIN VDE 0295, Cl. 5
- Partial stripping of insulation, the isolation remains on wire end
- Change of tools not necessary
- Quick and easy setting for the proper cross-section
- Stripping length from 3 to 20 mm
- Min. conductor length: 22 mm + stripping length
- Electric drive

General ordering data

Type	AIMESA VRM 6,20
Order No.	1120910000
Version	Automatic machines, Set of cutters
GTIN (EAN)	4032248901920
Qty.	1 pc(s).

Data sheet

Accessories
AIMESA VRM 6,20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	26.5 mm	Width (inches)	1.043 inch
Height	1.6 mm	Height (inches)	0.063 inch
Depth	20 mm	Depth (inches)	0.787 inch
Net weight	9 g		

Classifications

ETIM 4.0	EC002620	ETIM 5.0	EC002620
ETIM 6.0	EC002778	eClass 6.2	17-13-01-02
eClass 7.1	17-13-01-02	eClass 8.1	17-13-01-02
eClass 9.0	17-13-01-01	eClass 9.1	17-13-01-02

Approvals

ROHS	Conform
------	---------