

PAC
PAC-UNIV-D37F-F-2M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

Cable pre-confeccionado sub-d según IEC-807/
DIN41652

- Sub-d a Sub-d
- Sub-d a punteras
- Cable apantallado

General ordering data

Type	PAC-UNIV-D37F-F-2M
Order No.	1350500020
Version	Pre-assembled cable, PAC, Cable LiYCY, 12.2 ± 1 mm
GTIN (EAN)	4032248177349
Qty.	1 pc(s).

PAC

PAC-UNIV-D37F-F-2M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	584 g
------------	-------

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General Data

Connector PLC side	H0.25/10 (FERRULES 0.25mm ²)	Interface connector	SUB-D FEMALE 37P
Number of poles, min.	37-pole	Outer diameter	12.2 ± 1 mm
Cable	Cable LiYCY	Cable length	2 m
Material	PVC	Wire cross-section	0.25 mm ²

Electrical Data

Rated voltage (text)	≤ 60 Vdc ≤ 25 Vac	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	≤ 80 mΩ/m

Classifications

ETIM 5.0	EC000237	ETIM 6.0	EC000237
eClass 6.2	27-24-92-05	eClass 7.1	27-24-92-05
eClass 8.1	27-24-92-05	eClass 9.0	27-24-22-20
eClass 9.1	27-24-22-20		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Colours chart
--------------------	-------------------------------