

**Klippon POK (polyester empty enclosure)
KLIPPON COPL 082306**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Brass earthing plates (Earth Continuity Plate) for
the Klippon® POK enclosure**

In order to provide internal earthing (especially for the Ex version) earth continuity plates in an angled design are available for the Klippon® POK enclosure.

These internal earth continuity plates are for the usage of metal glands and the design of EMC applications; they offer enhanced protection and are available separately.

General ordering data

Type	KLIPPON COPL 082306
Order No.	1390950000
Version	Klippon POK (polyester empty enclosure), Earthing plate, Width: 33.5 mm, Material: Brass, polished, untreated
GTIN (EAN)	4050118191301
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)
KLIPPON COPL 082306**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	258 mm	Length (inches)	10.157 inch
Width	33.5 mm	Width (inches)	1.319 inch
Wall thickness, max.	0.8 mm	Wall thickness, min.	0.8 mm
Net weight	52.519 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

Material thickness	0.8 mm	Material	Brass
Surface finish	polished, untreated		

General information on accessories

Material	Brass	Material thickness	0.8 mm
Surface finish	polished, untreated		

Classifications

ETIM 5.0	EC002623	ETIM 6.0	EC002623
eClass 6.2	27-18-92-64	eClass 7.1	27-18-92-64
eClass 8.1	27-18-92-64	eClass 9.0	27-18-28-14
eClass 9.1	27-18-92-64		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP