SAIE-7/8S-4-0.2U-M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Similar to illustration



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-7/8S-4-0.2U-M20
Order No.	1418050000
Version	Built-in plugs, 7/8", M 20, No. of poles: 4
GTIN (EAN)	4050118221534
Qty.	1 pc(s).

SAIE-7/8S-4-0.2U-M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	30 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

General data

Cable glands	M 20	Coding	none
Conductor O.D.	-	Connection thread	7/8"
Contact material	CuZn	Contact surface	Gold-plated
Core cross-section	0.75 mm²	Housing main material	Zinc diecast, nickel-plated
No. of poles	4	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Rated current	8 A
Rated current	8 A (4- and 5-pole), 10 A (3-pole)	Rated voltage	300 V
Strand / cable length	0.2 m	Temperature range of housing	-25...+85 °C
Type of connection	Pin		

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC002635
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-01-02
eClass 9.1	27-44-01-03		

Approvals

Approvals	EAC
ROHS	Conform

Downloads


Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN

SAIE-7/8S-4-0.2U-M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Wiring diagram



Pole scheme

