
Connecting elements
H35,0/32 S BE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H35,0/32 S BE
Order No.	1418340000
Version	Wire-end ferrule, insulated, 21 mm, 18 mm, beige
GTIN (EAN)	4050118221725
Qty.	50 pc(s).
Packaging	loose

Connecting elements
H35,0/32 S BE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	32 mm	Width (inches)	1.26 inch
Net weight	1,450 g		

Technical data

Version	insulated

Wire-end ferrules

Collar diameter (D2)	12.7 mm	Colour code	Weidmüller
Conductor cross-section	35 mm²	Contact surface diameter (D1)	8.3 mm
Contact surface length (L2)	18 mm	L1 in mm	32 mm
Metal sleeve thickness (S1)	0.2 mm	Plastic collar thickness (S2)	0.4 mm
Stripping length	21 mm	Wire connection cross section AWG, max.	AWG 2

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01	eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01

Approvals

ROHS	Conform

Downloads

Engineering Data	EPLAN

Connecting elements
H35,0/32 S BE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

