

**Connecting elements
H0,5/14 OR SP**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



- supplied loose in poly-bag
- in multi-pack bag (5 x 100 pcs.)
- Linked of wire-end ferrule strips (50 pcs.)
- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Type | H0,5/14 OR SP |
| Order No. | 1476230000 |
| Version | Wire-end ferrule, insulated, 10 mm, 8 mm, orange |
| GTIN (EAN) | 4050118283174 |
| Qty. | 100 pc(s). |

Data sheet

**Connecting elements
H0,5/14 OR SP**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|----------------|------------|
| Width | 14 mm | Width (inches) | 0.551 inch |
| Net weight | 0.018 g | | |

Technical data

| | |
|---------|-----------|
| Version | insulated |
|---------|-----------|

Wire-end ferrules

| | | | |
|-----------------------------|---------------------|---|------------|
| Collar diameter (D2) | 2.6 mm | Colour code | Weidmüller |
| Conductor cross-section | 0.5 mm ² | Contact surface diameter (D1) | 1 mm |
| Contact surface length (L2) | 8 mm | L1 in mm | 14 mm |
| Metal sleeve thickness (S1) | 0.15 mm | Plastic collar thickness (S2) | 0.25 mm |
| Stripping length | 10 mm | Wire connection cross section AWG, max. | AWG 20 |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000005 | ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 | ETIM 6.0 | EC000005 |
| eClass 5.1 | 27-40-02-01 | eClass 6.2 | 27-40-02-01 |
| eClass 7.1 | 27-40-02-01 | eClass 8.1 | 27-40-02-01 |
| eClass 9.0 | 27-40-02-01 | eClass 9.1 | 27-40-02-01 |

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [EPLAN](#)