

## **cable lug, terminal end KRN-M16/-240**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

### **General ordering data**

|            |                                              |
|------------|----------------------------------------------|
| Type       | KRN-M16/-240                                 |
| Order No.  | <a href="#">1495510000</a>                   |
| Version    | cable lug, terminal end, 240 mm <sup>2</sup> |
| GTIN (EAN) | 4050118304770                                |
| Qty.       | 25 pc(s).                                    |

## cable lug, terminal end KRN-M16/-240

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

|        |         |            |         |
|--------|---------|------------|---------|
| Weight | 13.56 g | Net weight | 134.2 g |
|--------|---------|------------|---------|

### Technical data

|         |                       |
|---------|-----------------------|
| Version | Euro series, standard |
|---------|-----------------------|

### Connectors

|                                |                     |                                |         |
|--------------------------------|---------------------|--------------------------------|---------|
| Conductor cross-section        | 240 mm <sup>2</sup> | Connection length (l)          | 69.5 mm |
| Flange width (b)               | 38 mm               | Hole                           | M 16    |
| Inside diameter of flange (d2) | 17 mm               | Inside diameter of shaft (d1)  | 21 mm   |
| Insulation                     | not available       | Outside diameter of shaft (d3) | 26 mm   |
| Shaft length (a)               | 35 mm               |                                |         |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001509    | ETIM 4.0   | EC001509    |
| ETIM 5.0   | EC001051    | ETIM 6.0   | EC001051    |
| eClass 6.2 | 27-40-02-05 | eClass 7.1 | 27-40-02-04 |
| eClass 8.1 | 27-40-02-05 | eClass 9.0 | 27-40-02-05 |
| eClass 9.1 | 27-40-02-05 |            |             |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                      |
|--------------------|--------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a> |
| Engineering Data   | <a href="#">EPLAN</a>                |
| Engineering Data   | <a href="#">STEP</a>                 |

### cable lug, terminal end KRN-M16/-240

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

