

**cable lug, terminal end
KP-M14/-70**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KP-M14/-70
Order No.	1498560000
Version	cable lug, terminal end, 70 mm ²
GTIN (EAN)	4050118307696
Qty.	50 pc(s).

**cable lug, terminal end
KP-M14/-70**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Weight	6 g	Net weight	60 g
--------	-----	------------	------

Technical data

Version	DIN series 46235, standard
---------	-------------------------------

Connectors

Conductor cross-section	70 mm ²	Connection length (l)	55.5 mm
Flange width (b)	24 mm	Hole	M 14
Identification number Cu	16 K	Inside diameter of flange (d2)	15 mm
Inside diameter of shaft (d1)	11.3 mm	Insulation	not available
Outside diameter of shaft (d3)	16.5 mm	Shaft length (a)	28 mm

Classifications

ETIM 3.0	EC001509	ETIM 4.0	EC001509
ETIM 5.0	EC001050	ETIM 6.0	EC001050
eClass 6.2	27-40-02-05	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-03	eClass 9.0	27-40-02-03
eClass 9.1	27-40-02-03		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

Data sheet**cable lug, terminal end
KP-M14/-70**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings