

PZ PK 10/120**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for tubular and compression cable lugs with swivel crimping star.**

- Integrated crimping star for different cross-sections
- Hexagon crimping tools for compression cable lugs
- WM-From crimping tools for tubular cable lugs
- wide processing range up to 70 or 120 mm²

General ordering data

Type	PZ PK 10/120
Order No.	1500480000
Version	10mm ² , 120mm ²
GTIN (EAN)	4050118309089
Qty.	1 pc(s).

PZ PK 10/120

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Depth	660 mm	Depth (inches)	25.984 inch
Weight	4,100 g	Net weight	3,800 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Crimp inserts

Crimp cross-section aluminium	10 ... 70 mm ²	Crimping width	5 mm
-------------------------------	---------------------------	----------------	------

Description of contact

Crimping range, min.	10 mm ²	Crimping range, max.	120 mm ²
----------------------	--------------------	----------------------	---------------------

Classifications

ETIM 5.0	EC000168	ETIM 6.0	EC000168
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------