

ES APG 80 AEH 150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Type	ES APG 80 AEH 150
Order No.	1502100000
Version	150mm ² , Trapezoidal crimp
GTIN (EAN)	4050118310085
Qty.	1 pc(s).

ES APG 80 AEH 150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 472.7 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Crimp inserts

Crimp cross-section copper	150	Crimping width in mm	38
Crimping width	38 mm		

Description of contactCrimping range, max. 150 mm²**tool data crimping**

Crimping type/profile Trapezoidal crimp

Classifications

ETIM 5.0	EC000168	ETIM 6.0	EC001282
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-90-90
eClass 9.1	21-01-90-90		

DownloadsBrochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)