

**ES APG 80 HEX 120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

**General ordering data**

Type	ES APG 80 HEX 120
Order No.	<a href="#">1502700000</a>
Version	Hexagonal crimping
GTIN (EAN)	4050118310931
Qty.	1 pc(s).

## ES APG 80 HEX 120

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

# Technical data

### Dimensions and weights

Net weight 322 g

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Crimp inserts

Crimp cross-section copper	120	Crimping width in mm	10
Identification number	20	Crimping width	10 mm

### tool data crimping

Crimping type/profile Hexagonal crimping

### Classifications

ETIM 5.0	EC000168	ETIM 6.0	EC001282
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-90-90
eClass 9.1	21-01-90-90		

### Downloads

Brochure/Catalogue [CAT 3 HDC 17/18 EN](#)  
[CAT 6 TOOLS 15/16 EN](#)