

**ES APG 80 DIN 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

**General ordering data**

Type	ES APG 80 DIN 50
Order No.	<a href="#">1502880000</a>
Version	50mm <sup>2</sup> , Indent crimping
GTIN (EAN)	4050118310450
Qty.	1 pc(s).

**ES APG 80 DIN 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 359.4 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Crimp inserts**

Crimp cross-section copper	50	Crimping width in mm	16
Crimping width	16 mm		

**Description of contact**Crimping range, max. 50 mm<sup>2</sup>**tool data crimping**

Crimping type/profile Indent crimping

**Classifications**

ETIM 5.0	EC000168	ETIM 6.0	EC001282
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-90-90
eClass 9.1	21-01-90-90		

**Downloads**Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)