

ES EPG 45 WM 150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

General ordering data

Type	ES EPG 45 WM 150
Order No.	1994550000
Version	WM crimp
GTIN (EAN)	4050118379785
Qty.	1 pc(s).

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 2.75 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Crimp inserts

Crimp cross-section copper	150	Crimping width in mm	5
Crimping width	5 mm		

tool data crimping

Crimping type/profile WM crimp

Classifications

ETIM 5.0	EC000168	ETIM 6.0	EC001282
eClass 6.2	21-04-38-11	eClass 9.0	21-04-90-90
eClass 9.1	21-01-90-90		