

HPG 60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Type	HPG 60
Order No.	2453820000
Version	6mm ² , 300mm ² , Hexagonal crimping, WM crimp, Indent crimping, Trapezoidal crimp, Oval crimp
GTIN (EAN)	4050118468427
Qty.	1 pc(s).

HPG 60

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	500 mm	Width (inches)	19.685 inch
Weight	4,350 g	Net weight	6,520 g

Description of contact

Crimping range, min.	6 mm ²	Crimping range, max.	300 mm ²
----------------------	-------------------	----------------------	---------------------

tool data crimping

Drive	Manual - hydraulic	Crimping type/profile	Hexagonal crimping, WM crimp, Indent crimping, Trapezoidal crimp, Oval crimp
-------	--------------------	-----------------------	--

Classifications

ETIM 5.0	EC000168	ETIM 6.0	EC000168
eClass 6.2	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		