

CAN SUB-D SK TERM PS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Type	CAN SUB-D SK TERM PS
Order No.	1550590000
Version	
GTIN (EAN)	4050118357134
Qty.	1 pc(s).

CAN SUB-D SK TERM PS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	100 g
------------	-------

Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical specifications for sub-D connector

BUS PG interface	D-Sub 9-pole, Pin	BUS interface	D-Sub 9-pole, Pin
BUS, cable interface	Screw connection	Data rate	1 Mbps
Housing main material	ZnAl	Humidity	Max. 75% at +25°C, non-condensing
Interlock	UNC4-40	Outgoing elbow	90°
Plugging cycles	≥ 200	Protection degree	IP30
Temperature range of housing	-20...+70 °C	Terminating resistor available	Yes

Classifications

ETIM 5.0	EC002640	ETIM 6.0	EC001132
eClass 6.2	27-26-07-07	eClass 7.1	27-44-03-07
eClass 8.1	27-44-03-07	eClass 9.0	27-44-03-02
eClass 9.1	27-44-03-90		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN
--------------------	-----------------------------------