

SAIE-M12S-CD-2.0A HW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M12S-CD-2.0A HW
Order No.	2484420200
Version	Built-in plugs, M12, PG 9, No. of poles: 5, 2 m
GTIN (EAN)	4050118495935
Qty.	1 pc(s).

SAIE-M12S-CD-2.0A HW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	120 g
------------	-------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Bending radius, min., moving	10 x cable diameter	Bending radius, min., stationary	5 x cable diameter
Cable diameter, max.	7.5 mm	Cable diameter, min.	6.9 mm
Cable glands	PG 9	Cable length	2 m
Coding	A	Conductor O.D.	-
Connection thread	M12	No. of poles	5
Plugging cycles	≥ 100 (M12)	Pollution severity	3
Protection degree	IP68	Rated current	4 A
Rated voltage	125 V	Sheathing colour	violet
Shield connection	Yes	Strand / cable length	2 m
Temperature range of housing	-5 ... +70 °C		

Classifications

ETIM 6.0	EC002638	eClass 6.2	27-26-07-02
eClass 9.0	27-44-03-09	eClass 9.1	27-44-03-09

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN
--------------------	-----------------------------------

SAIE-M12S-CD-2.0A HW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

