

CMA-3151-250-AO-24DC-05**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The pluggable current transformers are particularly suitable for installation on the busbar.

Advantages:

- Screwless connection system with tension-clamp terminal.
- Time-saving connection option for solid and flexible conductors.
- Shock-proof and resistant to vibration, high mechanical retention forces.
- High current resistance

General ordering data

Type	CMA-3151-250-AO-24DC-05
Order No.	1531930000
Version	Current-measuring transducer, Primary current: 250 A, Secondary current : 4 - 20 mA, 1 VA, Tolerance class: 0,5
GTIN (EAN)	4050118337204
Qty.	1 pc(s).

CMA-3151-250-AO-24DC-05

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	80 mm	Width (inches)	3.15 inch
Height	117.8 mm	Height (inches)	4.638 inch
Depth	71 mm	Depth (inches)	2.795 inch
Net weight	250 g		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Dimensions of live conductors

Rail	30 x 10 mm	Round conductor	28 mm
------	------------	-----------------	-------

Electrical attributes

Load	1 VA	Primary current	250 A
Secondary current	4 - 20 mA	Secondary current max.	20 mA
Secondary current, min.	4 mA	Tolerance class	0,5

Technical data

Insulation class	E	Nominal frequency	50 Hz
Thermal rated continuous current $I_{\text{thermal}} 1.5 \times I_{\text{rated}}$			

Classifications

ETIM 5.0	EC002048	ETIM 6.0	EC002048
eClass 6.2	27-21-09-02	eClass 7.1	27-21-09-02
eClass 8.1	27-21-09-02	eClass 9.0	27-21-09-02
eClass 9.1	27-21-09-02		

Approvals

ROHS	Conform
------	---------

CMA-3151-250-AO-24DC-05

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

