

**Klippon POK (polyester empty enclosure)
POK MOPL 4040 MINI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Integrate, expand and customise - the perfect supplement to every application**

The consistent structure of system accessories for the Klippon® POK enclosure range allows you to easily adapt the enclosure to meet the specific requirements of every application.

The range includes:

- Mounting plates
- Earthing plates
- Mounting feet

Our assembly service includes the delivery of the enclosure ready to be connected and suitable for every application.

General ordering data

Type	POK MOPL 4040 MINI
Order No.	1534440000
Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 359 mm, Width: 383 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, galvanized, silver
GTIN (EAN)	4050118337891
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)
POK MOPL 4040 MINI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	383 mm	Width (inches)	15.079 inch
Height	359 mm	Height (inches)	14.134 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Mounting dimension - width	372 mm	Mounting dimension - height	250 mm
Net weight	1,630 g		

General information

Material thickness	1.5 mm	Material	Sheet steel, galvanized
Surface finish	galvanized		

General information on accessories

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Mounting dimension - height	250 mm	Mounting dimension - width	372 mm
Surface finish	galvanized		

Classifications

ETIM 6.0	EC000213	eClass 6.2	27-18-92-61
eClass 9.0	27-40-06-39	eClass 9.1	27-18-92-90

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP