SAIE-M8B-3-1.5U-FP-M8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M8B-3-1.5U-FP-M8
Order No.	2020870000
Version	Built-in plugs, M8 thread, Female socket, straight, M 8, No. of poles: 3, 1.5 m
GTIN (EAN)	4050118402902
Qty.	1 pc(s).

SAIE-M8B-3-1.5U-FP-M8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	26.8 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Standards

Connector standard	IEC 61076-2-104

General data

Cable glands	M 8	Cable length	1.5 m
Coding	none	Conductor O.D.	-
Connection thread	M8 thread	Contact surface	Gold-plated
Housing main material	Brass, nickel-plated	No. of poles	3
Protection degree	IP67, when screwed in	Strand / cable length	1.5 m
Type of connection	Socket connector		

Classifications

ETIM 6.0	EC002635	eClass 6.2	27-26-07-02
eClass 9.0	27-44-01-02	eClass 9.1	27-44-01-03

Approvals

ROHS	Conform

Downloads

Brochure/Catalogue	FL FIELDWIRING EN

SAIE-M8B-3-1.5U-FP-M8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Pole scheme

