

**Klippon POK (polyester empty enclosure)
POK MOPL 2540 MINI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Integrate, expand and customise - the perfect supplement to every application

The consistent structure of system accessories for the Klippon® POK enclosure range allows you to easily adapt the enclosure to meet the specific requirements of every application.

The range includes:

- Mounting plates
- Earthing plates
- Mounting feet

Our assembly service includes the delivery of the enclosure ready to be connected and suitable for every application.

General ordering data

Type	POK MOPL 2540 MINI
Order No.	1534420000
Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 204 mm, Width: 382 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, galvanized, silver
GTIN (EAN)	4050118338164
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)
POK MOPL 2540 MINI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	382 mm	Width (inches)	15.039 inch
Height	204 mm	Height (inches)	8.031 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Mounting dimension - width	372 mm	Mounting dimension - height	100 mm
Net weight	930 g		

General information

Material thickness	1.5 mm	Material	Sheet steel, galvanized
Surface finish	galvanized		

General information on accessories

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Mounting dimension - height	100 mm	Mounting dimension - width	372 mm
Surface finish	galvanized		

Classifications

ETIM 6.0	EC000213	eClass 6.2	27-18-92-61
eClass 9.0	27-40-06-39	eClass 9.1	27-18-92-90

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	STEP