

CMA-CTM-7-40-1A-0.3VA-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Product image

similar to the product

General ordering data

Type	CMA-CTM-7-40-1A-0.3VA-1
Order No.	2556040000
Version	Primary current: 40 A, Secondary current max.: 1 A, Load: 0.3 VA, Tolerance class: 1
GTIN (EAN)	4050118566413
Qty.	1 pc(s).

CMA-CTM-7-40-1A-0.3VA-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	27.5 mm	Width (inches)	1.083 inch
Height	46.5 mm	Height (inches)	1.831 inch
Depth	19 mm	Depth (inches)	0.748 inch
Net weight	64 g		

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-5 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-25 °C
Operating temperature	-5 °C...50 °C	Storage temperature	-25 °C...70 °C

Technical data

Insulation class	E	Nominal frequency	50 Hz
Operating voltage $U_{\max}$, max.	0,72 kV	Thermal rated continuous current I_{thermal}	1.0 x I_{rated}

Dimensions of live conductors

Round conductor	7.6 mm
-----------------	--------

Electrical attributes

Load	0.3 VA	Primary current	40 A
Secondary current max.	1 A	Tolerance class	1

Classifications

ETIM 6.0	EC002048	eClass 6.2	27-21-09-02
eClass 9.0	27-21-09-02	eClass 9.1	27-21-09-02

Approvals

ROHS	Conform
------	---------

CMA-CTM-7-40-1A-0.3VA-1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

