

**Klippon POK (polyester empty enclosure)  
POK MOPL 1636 MINI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Integrate, expand and customise - the perfect supplement to every application**

The consistent structure of system accessories for the Klippon® POK enclosure range allows you to easily adapt the enclosure to meet the specific requirements of every application.

The range includes:

- Mounting plates
- Earthing plates
- Mounting feet

Our assembly service includes the delivery of the enclosure ready to be connected and suitable for every application.

**General ordering data**

Type	POK MOPL 1636 MINI
Order No.	<a href="#">1534380000</a>
Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 113 mm, Width: 342 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, galvanized, silver
GTIN (EAN)	4050118338317
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)  
POK MOPL 1636 MINI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	342 mm	Width (inches)	13.465 inch
Height	113 mm	Height (inches)	4.449 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Mounting dimension - width	332 mm	Mounting dimension - height	76 mm
Net weight	408 g		

**General information**

Material thickness	1.5 mm	Material	Sheet steel, galvanized
Surface finish	galvanized		

**General information on accessories**

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Mounting dimension - height	76 mm	Mounting dimension - width	332 mm
Surface finish	galvanized		

**Classifications**

ETIM 6.0	EC000213	eClass 6.2	27-18-92-61
eClass 9.0	27-40-06-39	eClass 9.1	27-18-92-90

**Approvals**

Approvals


**Downloads**

Brochure/Catalogue	<a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">STEP</a>