

PAC-D25M-D25F-HF-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

Cable pre-confeccionado sub-d según IEC-807/
DIN41652

- Sub-d a Sub-d
- Sub-d a punteras
- Cable apantallado

General ordering data

Type	PAC-D25M-D25F-HF-3M
Order No.	2426160030
Version	
GTIN (EAN)	4032248343362
Qty.	1 pc(s).

PAC-D25M-D25F-HF-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	745 g
------------	-------

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

General Data

Connector PLC side	SUB-D FEMALE 25P	Interface connector	SUB-D MALE 25P
Number of poles, min.	25-pole	Cable	Cable LIHCH
Cable length	3 m	Wire cross-section	0.25 mm ²

Electrical Data

Rated voltage (text)	$\leq 60 \text{ Vdc} \leq 25 \text{ Vac}$	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	$\leq 80 \text{ m}\Omega/\text{m}$

Classifications

ETIM 6.0	EC000237	eClass 6.2	27-24-92-05
eClass 9.0	27-24-22-20	eClass 9.1	27-24-22-20

Approvals

ROHS	Conform
------	---------