

**Cabtite (cable entry system)
CABTITE FRL 16/8 BK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

General ordering data

Type	CABTITE FRL 16/8 BK
Order No.	2584220000
Version	Locking frame, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 11.3 mm, Width: 68.8 mm, Depth: 11.3 mm, -40 °C...120 °C
GTIN (EAN)	4050118616590
Qty.	10 pc(s).

Cabtite (cable entry system) CABTITE FRL 16/8 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	125 mm	Length (inches)	4.921 inch
Width	68.8 mm	Width (inches)	2.709 inch
Height	11.3 mm	Height (inches)	0.445 inch
Height of lowest version	11.3 mm	Depth	11.3 mm
Depth (inches)	0.445 inch	Mounting dimension - width	32 mm
Mounting dimension - height	103 mm	Net weight	29.7 g
Diameter	5.5 mm		

General information

Tightening torque	3 Nm	Opening width	40 mm
Opening length	85 mm	UL 94 flammability rating	V-0
Halogen	No	Silicone	No
Material	Polyamide, glass fibre-reinforced		

Classifications

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

Approvals

Approvals



ROHS Conform

Downloads

User Documentation [Cabtite Installation Instructions](#)