

W-Series
WQB 6 WTL 6/4 FF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Type	WQB 6 WTL 6/4 FF
Order No.	2551490000
Version	W-Series, Cross-connector, For the terminals, No. of poles: 6
GTIN (EAN)	4050118577648
Qty.	10 pc(s).

W-Series
WQB 6 WTL 6/4 FF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	62.6 mm	Width (inches)	2.465 inch
Height	29.32 mm	Height (inches)	1.154 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	15 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Colour	orange
--------	--------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Dimensions

Pitch in mm (P)	11.1 mm
-----------------	---------

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	eClass 6.2	27-14-92-14
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40

Approvals

ROHS	Conform
------	---------