

**W-Series**  
**WQB 12 WTL 6/4 FF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

|            |                                                                |
|------------|----------------------------------------------------------------|
| Type       | WQB 12 WTL 6/4 FF                                              |
| Order No.  | <a href="#">2552080000</a>                                     |
| Version    | W-Series, Cross-connector, For the terminals, No. of poles: 12 |
| GTIN (EAN) | 4050118577655                                                  |
| Qty.       | 10 pc(s).                                                      |

**W-Series**  
**WQB 12 WTL 6/4 FF**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 129.1 mm | Width (inches)  | 5.083 inch |
| Height     | 29.32 mm | Height (inches) | 1.154 inch |
| Depth      | 5 mm     | Depth (inches)  | 0.197 inch |
| Net weight | 30 g     |                 |            |

**Temperatures**

|                           |               |                           |       |
|---------------------------|---------------|---------------------------|-------|
| Storage temperature, max. | 40 °C         | Storage temperature, min. | 10 °C |
| Storage temperature       | 10 °C...40 °C |                           |       |

**Material data**

|        |        |
|--------|--------|
| Colour | orange |
|--------|--------|

**System specifications**

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

**Additional technical data**

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

**Dimensions**

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 11.1 mm |
|-----------------|---------|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 41 A |
|---------------|------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC000489    | eClass 6.2 | 27-14-92-14 |
| eClass 9.0 | 27-14-11-40 | eClass 9.1 | 27-14-11-40 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|