



Cat.6A S/FTP PIMF LSOH, Red, 1.5m

Part No.: 47163

Description

- Plug: RJ45 shielded, Snagless (line protection), gold-plated contacts (8µm)
- Cable: 27 AWG, 4 wire pairs (PIMF: pairs in metal foil), LSOH (halogen-free)
- Gigabit compatible as well as 10GBase-T
- 10/100/1000 / 10GBase-T support
- Corresponds to: ANSI / TIA-568-C.2
- Used according to colour code: TIA / EIA-568-B
- Colour: Red
- Available in lengths from 0.3m to 30m
- 10 year warranty