

**Cabtite (cable entry system)
CABTITE FR 24/10 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

General ordering data

Type	CABTITE FR 24/10 BK
Order No.	2583800000
Version	Frame, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 19.6 mm, Width: 70 mm, Depth: 19.6 mm, -40 °C... 120 °C, IP54, IP65, IP66
GTIN (EAN)	4050118616682
Qty.	1 pc(s).

Cabtite (cable entry system) CABTITE FR 24/10 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	153 mm	Length (inches)	6.024 inch
Width	70 mm	Width (inches)	2.756 inch
Height	19.6 mm	Height (inches)	0.772 inch
Height of lowest version	19.6 mm	Depth	19.6 mm
Depth (inches)	0.772 inch	Mounting dimension - width	32 mm
Mounting dimension - height	130 mm	Net weight	60.95 g
Diameter	5.5 mm		

General information

Tightening torque	3 Nm	Opening width	46 mm
Opening length	113.5 mm	UL 94 flammability rating	V-0
Sealing element	2 large sealing elements and 4 small sealing elements or 1 large sealing element and 6 small sealing elements or 10 small sealing elements	Halogen	No
Silicone	No	Sealing	TPE
Material	Polyamide, glass fibre-reinforced		

Classifications

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	STEP
User Documentation	Cabtite Installation Instructions

Cabtite (cable entry system) CABTITE FR 24/10 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

