

Gauge rings
WCU 650 PC CABLE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



With the fully encapsulated WCU 501 and WCU 650 logic modules, you monitor, control and regulate your processes - even under extreme environmental conditions. In this regard, the WCU series offers optimum dimensions, performance, robustness and user-friendliness. The graphic and intuitive Micon-L programming environment enables flexible switching of the analogue and digital inputs, plus the digital outputs too. The scope of both the software and the hardware can be expanded to suit customer requirements upon request. .

General ordering data

Type	WCU 650 PC CABLE
Order No.	2515020000
Version	USB 2.0
GTIN (EAN)	4050118528749
Qty.	1 pc(s).

Gauge rings WCU 650 PC CABLE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	1,500 mm	Length (inches)	59.055 inch
Net weight	75 g		

Temperatures

Operating temperature, max.	60 °C	Operating temperature, min.	-20 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-30 °C
Operating temperature	-20 °C...60 °C	Storage temperature	-30 °C...60 °C

General data

Interface	USB 2.0	Type of connection	USB A
-----------	---------	--------------------	-------

EMC / shock / vibration

Shock resistance	min. 100 m/s ² (10 g)	Vibration resistance	min. 50 m/s ² (5 g) @ 10... 150 Hz
------------------	----------------------------------	----------------------	--

Classifications

ETIM 6.0	EC000237	eClass 6.2	27-14-30-90
eClass 9.0	27-24-22-20	eClass 9.1	27-24-22-20

Approvals

ROHS	Conform
------	---------