

# 4G LTE Mobile Wi-Fi

Go Anywhere Connect Everywhere







## Highlights

#### Share 4G LTE Connection on the Go

The M7200 features a compact, elegant design very suitable for travel, business trips, outdoor activities or wherever you may be.

#### Easy Management with the tpMiFi App

With the tpMiFi App, you can easily access and manage the M7200 from your connected iOS/Android devices. The tpMiFi app allows you to establish data limits, control which devices can access your Wi-Fi, and send messages.





### Features





#### Lightning 4G LTE

- Lightning generation 4G LTE Supports 4G LTE network, compatible with 3G network
- The Faster Connections Reaches up to 150Mbps download speed and 50Mbps upload speed, to enjoy HD movies without interruption, download files in seconds, and hold a video chat without dropouts

#### **Convenient Hotspot**

- Plug and Play Just insert a SIM card and power on to create a stable Wi-Fi hotspot to share on the move
  2000mAh 2000mAh rechargeable battery capacity
- High-Speed Hotspot Share 2.4GHz Wi-Fi at speed of 300Mbps
  with up to 10 Wi-Fi devices
  480 hours 480 hours of standby

#### 8 Hours Usage

- · 8 hours 8 hours of 4G sharing
- \* Actual battery time may vary due to different user environments

## **Specifications**

#### Hardware

- Interface: 1 micro USB port, 1 SIM card slot
- Button: Power Button, Reset Button
- · LED: Wi-Fi LED, Internet LED, Battery LED
- External Power Supply: 5V/1A
- Dimensions (W x D x H):  $3.7 \times 2.2 \times 0.8$  in. ( $94 \times 56.7 \times 19.8$ mm)
- · Antenna: Internal Antennas

#### **Wireless**

- Network Type:
- System Requirements: 4G: FDD-LTE: B1/B3/B7/B8/B20 (2100/1800/2600/900/800MHz) Windows 10/8/7/Vista/XP, Mac OS, Android, iOS, TDD-LTE: B38/B40/B41 (2600/2300/2500MHz) Windows Phone 3G: DC-HSPA+/HSPA/UMTS: B1/B8(2100/900MHz) Environment Operating Temperature:  $0^{\circ}C \sim 35^{\circ}C$  ( $32^{\circ}F \sim 95^{\circ}F$ ) Storage Temperature: -20°C~60°C (-4°F ~140°F) Operating Humidity: 10%~90% non-condensing Storage Humidity: 5%~90% non-condensing Package Contents Mobile Wi-Fi M7200 11g 54Mbps: -74dBm; Micro USB Cable 11n HT20 MCS7: -70dBm; 2000mAh Battery 11n HT40 MCS7: -68dBm; Quick Installation Guide
- · Wireless Standards: IEEE 802.11b/g/n 2.4GHz
- Frequency: 2.4GHz
- · Wireless Speed: 300Mbps
- Transmit Power: <20dBm
- Reception Sensitivity: 11b 11Mbps: -87.5dBm;

- · Wireless Security: Support WPA-PSK/WPA2-PSK,Wireless MAC Filtering, Enable/Disable SSID Broadcast
- · DHCP: Server, Client, DHCP Client List



For more information, please visit http://www.tp-link.com/en/products/details/M7200.html or scan the QR code left

Specifications are subject to change without notice. TP-Link is a registered trademark of TP-Link Technologies Co., Ltd. All rights reserved.

#### Others

Certification: CE, RoHS

www.tp-link.com

**TP-Link** 4G LTE Mobile Wi-Fi M7200