

Dino-Lite AM4113T-FV2W



The VW series has two types of LED lights that are switchable between white and UV light. This model has a filter to filter out the returning UV light so that an image with natural colors can be obtained. Also available without return filter (model AM4113T-VW) and in a version with 390-400nm LEDs (model AM4113T-FVW).

Model	AM4113T-FV2W
Resolution	1,3 megapixel (1280x1024 pixels)
Magnification	10x~70x, 200x
Interface	USB 2.0, High speed USB transmission
Nr. of LED's	4+4
LED on/off switchable	Yes
LED color	~375 nm UV + white
Housing	Composite
Microtouch	Yes
Magnification lock	Yes
Output	Picture, video and time-lapsed video
Video Frame Rate	up to 30 frames-per-second, 15fps at 1.3M
Measurement	Yes (line, radius, circle, 3-point circle, etc.)
Calibration	Yes
Filter/Diffuser	No (MSAA111A1 diffuser cap available as optional accessory)
Compatibility	Windows XP, Vista, 7, 8 & 10, MacOS 10.9 and up
Software (Included)	Windows: DinoCapture 2.0, Mac: DinoXcope

