



30W

VT-4031 30W SMD FLOODLIGHTS COLORCODE:4000K BLACK BODY

Lumens 2550	Beam Angle 110	Dimensions 185x163x26mm
-----------------------	--------------------------	-----------------------------------

Day White
SKU:5953


2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Instant Start:	0-100% in 11s	Dimmable:	No
Watts:	30	Warranty (Years):	2
Lumens:	2550	PF:	>0.9
Beam Angle:	110	CRI:	>70
Unit Color:	Black	Operation Temperature:	-25 to +50°C
Long life:	20,000 Hours	Input Power:	AC:220-240V,50Hz
LED Chip Type:	SMD2835	Sensor Compatibility:	Yes
IP Rating:	IP65		



Features

- ✓ Perfect replacement of Metal Halide Floodlight, High Pressure Sodium Floodlight & Halogen Floodlight
- ✓ Available in different color options of White , Day White, Warm White and RGB
- ✓ Fascia glass sealed with SILICONE RUBBER ensuring superior waterproof / airtight performance
- ✓ Premium Quality Aluminium Alloy body
- ✓ High Power LED chip
- ✓ Corrosion Resistant
- ✓ Built in driver - no external power supply required
- ✓ Excellent coverage for area and façade lighting
- ✓ Available from 10W up to 1000W
- ✓ Application - Building Façade, Sports Facilities, Industrial, Commercial Bill Boards & Hoardings, Parking Lots etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.7175
Unit CBM	0.000969

Listing Details

EAN Code	3800157625463
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	900

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES