


Art.-No.	VE	PG	EAN
192204015	1	191	 4 008224 5 144 15

Three-phase power meter, 400V~ regenerated, uncertified, 10/40A



Technical data		192204015
Type of meter	Electromechanical	
Pole type	Three conductor	
Suitable for	Purchase	
Tariff type	One-tariff	
Tariff control	Internal	
Type of indication	Analogue	
Mounting method	Surface mounting	
Degree of protection (IP)	IP20	
Nominal current (I _n)	10A	
Max. current (I _{max})	40A	
Nominal voltage (U _n) L-L	400V	
Frequency	50Hz	
Escapement mechanism	Yes	
Calibrated	Yes	