

# LIGHTHOUSE core

Dimmable 430 lumen lantern with adjustable light direction. Built-in 1A USB port for charging phones and boosting tablets. USB rechargeable and features up to 350 hour runtime on low.



SKU# 32009  
UPC# 847974003794

|                             |  |
|-----------------------------|--|
| <b>Charge Time</b>          |  |
| GOAL ZERO Nomad 7           | 5-10 hrs                                     |
| USB source                  | 5 hrs  |
| <b>Run times:</b>           |  |
| One side lit (low power)    | 350+ hrs                                     |
| One side lit (high power)   | 8 hrs  |
| Both sides lit (low power)  | 200+ hrs                                     |
| Both sides lit (high power) | 4 hrs  |
| <b>Battery:</b>             |  |
| Cell chemistry              | Li-ion NMC                                   |
| Cell capacity               | 16.3Wh (3.7V, 4400mAh)                       |
| Lifecycles                  | hundreds of cycles                           |
| Shelf-life                  | Charge every 3-6 months                      |
| Management system           | Charging and low-battery protection built-in |
| <b>Light (Output):</b>      |  |
| LED (output)                | Warm white LEDs 430 Lumens                   |
| Color Temperature           | 3,500 Kelvin                                 |

|                       |                                  |
|-----------------------|----------------------------------|
| <b>Ports:</b>         |                                  |
| USB port (input)      | 5V, up to 1A (5W max)            |
| USB port (output)     | 5V, up to 1A (5W max), regulated |
| <b>General:</b>       |                                  |
| Chainable             | no                               |
| Weight                | 0.8 lbs (351 g)                  |
| Dimensions            | 5 x 4.5 in (12.7 x 11.4 cm)      |
| Operating usage temp. | 32-104 F (0-40 C)                |
| Certs.                | CE FC                            |
| Warranty              | 12 months                        |