

WIL-BM-JP-M12-3.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The WIL-STANDARD: 24V DC LED lamp, only 8mm high, with very high light output (1315 lm) and long service life (greater than 10,000 h).

Extremely robust construction, solid encapsulation and metal housing - waterproof (IP67).

Its 6500K colour temperature (daylight) makes it suitable for a wide range of applications.

Very easy to connect thanks to M12 connector. Low current consumption means that a 24V, 0.5A DC power supply is sufficient for operation.

General ordering data

Type	WIL-BM-JP-M12-3.0U
Order No.	2537710000
GTIN (EAN)	4050118549164
Qty.	1 pc(s).

Data sheet

WIL-BM-JP-M12-3.0U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 40 g

Temperatures

Operating temperature, max. 60 °C Operating temperature, min. -20 °C
 Operating temperature -20 - 60°C

Cable technical specifications

Cable Material PUR Sheathing colour black
 Cable length 3 m

Connection data

Connection thread M12 Tightening torque 0.8 Nm
 Wiring PIN 4: + (black), PIN 3: - (blue)

Electric data

Rated voltage (text) 24 V DC

Classifications

ETIM 6.0 EC002955 eClass 6.2 27-11-06-31

Approvals

Approvals



ROHS Conform

WIL-BM-JP-M12-3.0U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

