

SAIS-WDF-3+PE-M20-S-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIS-WDF-3+PE-M20-S-COD
Order No.	1460290000
Version	Panel feed-through, No. of poles: 4, Coding: S, M12, 630 V
GTIN (EAN)	4050118266412
Qty.	1 pc(s).

SAIS-WDF-3+PE-M20-S-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 20 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Standards

Certificate No. (cURus) E307231

General data

Cable glands	M 20	Coding	S
Conductor O.D.	-	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.14 mm ²	Connection thread	M12
Contact material	CuZn	Contact surface	Gold-plated
Housing main material	Zinc diecast	Insulation strength	10 ⁸ Ω
No. of poles	4	Plugging cycles	≥ 100
Pollution severity	3	Protection degree	IP67
Rated current	12 A	Rated current	12 A
Rated voltage	630 V	Shield connection	No
Temperature range of housing	-40 ... +85 ° C	Type of connection	Screw connection

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC002925
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-01-06
eClass 9.1	27-44-01-06		

Approvals

Approvals



ROHS Conform

DownloadsBrochure/Catalogue [CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)Engineering Data [STEP](#)

SAIS-WDF-3+PE-M20-S-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Pole scheme

