

APP CONTROLLED 1.0MP
720P WIFI DOORBELL



1280x720
720P

WiFi (2.4G network)

Battery operated or
8~24V power input



IP65
Water Resistant

Download the free
Caliber smart home app:



HWC 501



Hacker proof



Multi accessible



- Wireless doorbell with 720P HD camera
- Free "Caliber SMART HOME" app
- 1/4" Lens H.264 CMOS 1.0 MP
- Water resistant (IP65)
- Night vision
- Connect through WiFi (WiFi 2.4G network)
- Doorbell 'rings' on your phone
- Storage Max. 128 GB (Micro SD)
- Human detection (automatically receive a message)
- Dimensions base: (wired connection) 58mm (L) x 26mm (W) x 60mm (H)
- Dimensions base + battery pack: (wireless connected) 58mm (L) x 26mm (W) x 130mm (H)
- Power supply: 5V DC 1A (doorbell adapter (8~24V) and rechargeable battery included)
- Rechargeable battery pack (6000mAh)
- Smart Home - powered by Tuya
- Accessible by multiple devices (phones, tablets, etc)
- Hacker proof
- APP works with any internet connection (WiFi or mobile data)



- Sonnette sans fil avec caméra HD 720P
- Application gratuite « Caliber SMART HOME »
- Objectif 1/4 "CMOS H.264 1.0 MP
- Etanche (IP65)
- Vision nocturne
- Connexion via WiFi (réseau WiFi 2.4G)
- La sonnette retentit sur votre téléphone
- Mémoire max. 8 à 12 Go (micro SD)
- Envoi d'un message automatique lorsque quelqu'un presse la sonnette
- Dimensions (connexion câblée) 58 mm (L) x 26 mm (L) x 60 mm (H)
- Dimensions (connexion avec batterie) 58 mm (L) x 26 mm (L) x 130 mm (H)
- Alimentation : 5V DC 1A - adaptateur (8 ~ 24V) et batterie incluse
- Batterie (6000mAh)
- Smart Home - optimisé par Tuya
- Compatible avec plusieurs appareils (téléphones, tablettes, etc.)
- Anti piratage
- APP fonctionne avec toute connexion Internet (WiFi ou données cellulaires)



8 714505 046525



HWC with battery pack
'Rings' on your phone



Chime 'HWC 501CH'
sold separately

CALIBER SMART HOME
- LIVING IN COMFORT -

CALIBER.NL/CALIBERSMARTHOME
FOR DEMO'S & INSTRUCTIONS

This product requires a WiFi 2.4G network and a smart-phone/tablet

Wifi Freq range: 2402-2480 Mhz,
Max e.r.p.: <100mW/20dBm

Tuya word mark and logos are registered trademarks owned by Tuya, Inc. and any use of such marks by Caliber Europe BV is under license. Other trademarks and trade names are those of their respective owners.

CALIBER EUROPE BV

Kortakker 10 • 4264 AE Veen
The Netherlands • Tel: +31 416-699 000



www.caliber.nl