

THM
THM MT30X 76.2/50.8 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Type	THM MT30X 76.2/50.8 WS
Order No.	1378130000
Version	THM, Device markers, 50.8 x 76.5 mm, white
GTIN (EAN)	4050118179613
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

THM

THM MT30X 76.2/50.8 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	76.5 mm	Width (inches)	3.012 inch
Height	50.8 mm	Height (inches)	2 inch
Depth	0.08 mm	Depth (inches)	0.003 inch
Net weight	353.7 g		

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester	Material colour according to resistance code	9
Number per roll	500	Operating temperature range	-40... 150 °C
Printing method	Thermotransfer	UL 94 flammability rating	V-0
Version	Self-adhesive, halogen-free	Width	76.5 mm

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

THM THM MT30X 76.2/50.8 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

