

Accessories
GZ 7.0A/F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	GZ 7.0A/F
Order No.	1460630000
Version	Accessories, Fuse, 7 A
GTIN (EAN)	4050118266726
Qty.	10 pc(s).

Accessories
GZ 7.0A/F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	6.3 mm	Width (inches)	0.248 inch
Height	32 mm	Height (inches)	1.26 inch
Depth	6.3 mm	Depth (inches)	0.248 inch
Net weight	2.45 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Fuse cartridges

Cartridge fuse	G-Si. 6.3 x 32	Characteristics	quick-acting
Colour	Light Grey	Current	7 A
Rated breaking capacity	1.5 kA	Version	Fuse accessories

Rating data

Rated voltage	500 V	Rated current	7 A
---------------	-------	---------------	-----

Classifications

ETIM 3.0	EC000035	ETIM 6.0	EC000035
UNSPSC	30-21-18-14	eClass 5.1	27-14-20-07
eClass 6.2	27-14-20-07	eClass 7.1	27-14-20-90
eClass 8.1	27-14-20-01	eClass 9.0	27-14-20-01
eClass 9.1	27-14-20-01		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
--------------------	-------------------------------------