

VGM25-MS68 EMC 11-20SET**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The RockStar[®] HighPower housings are manufactured from high-strength die-cast aluminium and offer perfect protection against harsh environmental conditions thanks to continual optimisation. The multi-part housing gives users the opportunity to examine work processes down to the last step in the workflow.

General ordering data

Type	VGM25-MS68 EMC 11-20SET
Order No.	1463720000
Version	
GTIN (EAN)	4050118269871
Qty.	1 pc(s).

VGM25-MS68 EMC 11-20SET

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Length	63.5 mm	Length (inches)	2.5 inch
Net weight	94.44 g		

Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Cable diameter, max.	20 mm	Cable diameter, min.	11 mm
Cable glands	M 25, EMV	Material	Brass, nickel-plated
Sealing material	T80s	Series	HighPower
Type of sealing	Rubber ring		

Classifications

ETIM 5.0	EC001123	ETIM 6.0	EC000441
eClass 6.2	27-26-12-90	eClass 7.1	27-44-02-90
eClass 8.1	27-44-02-90	eClass 9.0	27-14-44-32
eClass 9.1	27-14-44-32		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN
Engineering Data	STEP